

Australian Government

National Measurement Institute Bradfield Road, West Lindfield NSW 2070

# **Certificate of Approval**

# NMI 6/4D/368

Issued by the Chief Metrologist under Regulation 60 of the National Measurement Regulations 1999

This is to certify that an approval for use for trade has been granted in respect of the instruments herein described.

Ohaus Model RS-15S Weighing Instrument

submitted by	Ohaus Corporation	on	
-	Unit 3, 220 Turner Street		
	Port Melbourne	VIC	3207

**NOTE:** This Certificate relates to the suitability of the pattern of the instrument for use for trade only in respect of its metrological characteristics. This Certificate does not constitute or imply any guarantee of compliance by the manufacturer or any other person with any requirements regarding safety.

This approval has been granted with reference to document OIML R 76, *Non-* automatic *weighing instruments, Part 1*, Edition 2006.

This approval becomes subject to review on 1/05/18, and then every 5 years thereafter.

Rev	Reason/Details	Date
0	Pattern & variant 1 approved – interim certificate issued	8/04/13
1	Pattern & variant 1 approved – certificate issued	11/06/13

#### DOCUMENT HISTORY

#### CONDITIONS OF APPROVAL

#### General

Instruments purporting to comply with this approval shall be marked with pattern approval number 'NMI 6/4D/368' and only by persons authorised by the submittor.

It is the submittor's responsibility to ensure that all instruments marked with this approval number are constructed as described in the documentation lodged with the National Measurement Institute (NMI) and with the relevant Certificate of Approval and Technical Schedule. Failure to comply with this Condition may attract penalties under Section 19B of the National Measurement Act and may result in cancellation or withdrawal of the approval, in accordance with document NMI P 106.

Auxiliary devices used with this instrument shall comply with the requirements of General Supplementary Certificate No S1/0B.

#### **Special Conditions of Approval:**

Certain aspects of this instrument (in particular label and ticket formats) are able to be configured by the user. Whilst NMI believes that acceptable label and ticket formats can be achieved for typical basic sales modes, it is also possible for the instrument to be configured to produce unacceptable formats, and use of some formats may be inappropriate for different sales modes. It is the responsibility of the user to ensure that acceptable and appropriate formats are used in any particular situation.

Signed by a person authorised by the Chief Metrologist to exercise their powers under Regulation 60 of the *National Measurement Regulations 1999.* 

**Dr A Rawlinson** 

## TECHNICAL SCHEDULE No 6/4D/368

#### 1. Description of Pattern

#### approved on 8/04/13

An Ohaus model RS-15S class I single interval self-indicating price-computing non-automatic weighing instrument (Table 1 and Figures 1 & 2) of 15 kg maximum capacity with a verification scale interval of 0.005 kg.

The instrument has an operator keyboard and LCD display integrated into the instrument body, and a customer display which is either column-mounted or mounted directly to the body (Figure 2). Both displays are used for the presentation of weight, unit price and price information, zero, net indications and functions relating to product look up (PLU) items. In addition when a tare or preset tare is operational a display of the tare value is provided.

Instruments are fitted with an integral printer, for printing of tickets.

Instruments display unit price to \$9999.99/kg, total price to \$99999.99, and have a product look up (PLU) facility.

The instrument operates from mains AC power (240 V AC, 50 Hz).

Instruments may be fitted with output sockets (output interfacing capability) for the connection of auxiliary and/or peripheral devices.

#### 1.1 Zero

A zero-tracking device may be fitted.

The initial zero-setting device of the pattern has a nominal range of not more than 20% of the maximum capacity of the instrument.

The instrument has a semi-automatic zero-setting device with a nominal range of not more than 4% of the maximum capacity of the instrument.

#### 1.2 Tare

A semi-automatic and/or non-automatic keyboard-entered pre-set subtractive tare device, each of up to 14.995 kg, may be fitted.

Pre-set tare values may be associated with product look up (PLU) items.

A separate display of tare values is provided.

#### 1.3 Display Check

A display check is initiated whenever power is applied.

#### 1.4 Networking

A number of instruments may be connected in a network to share common PLU data, for totalisation across instruments, and to accumulate and retrieve management information.

In addition, the instrument may be interfaced with a computer for the collection of management data, the downloading of PLU data.

Note: The weighing and price computing functions of each weighing instrument in the network are independent, and the removal, repair or replacement of a particular weighing instrument does not necessitate re-verification of any other weighing instrument in the network.

# 1.5 Levelling

The instrument is provided with adjustable feet and a level indicator, and adjacent to the level indicator is a notice advising that the instrument must be level when in use.

## 1.6 Interfaces

Instruments may be fitted with interfaces for the connection of auxiliary and/or peripheral devices. Any interfaces shall comply with clause 5.3.6 of document NMI R76 (the basic intent of which is that it shall not be possible to alter weighing results via the interfaces).

Any measurement data output from the instrument or its interfaces shall only be used for trade in compliance with Supplementary Certificate No S1/0/B (in particular in regard to the data and its format).

Instruments may be fitted with a cash drawer, and with an Ethernet and two RS232 serial data interfaces.

## 1.7 Software

The software is designated as number 72250797 (only the last six digits of the software number are displayed) and version d non-legally relevant software as shown Figure 3.

The software version and number can be seen in the switch-on display sequence (when the power is first applied to the instrument).

#### **1.8 Verification Provision**

Provision is made for the application of a verification mark.

#### 1.9 Sealing Provision

Provision is made for access to the calibration switch which is located beneath the load receptor to be sealed by means of two destructible labels placed over the access holes as shown in (Figure 4).

#### 1.10 Descriptive Markings and Notices

Instruments carry the following markings:

Manufacturer's mark, or name written in full Indication of accuracy class	Ohaus Corporation	
Pattern approval mark for the instrument	NMI 6/4D/368	
Maximum capacity	<i>Max</i> g or kg	#1
Minimum capacity	<i>Min</i> g or kg	#1
Verification scale interval	e = g or kg	#1
Maximum subtractive tare	<i>T</i> = g or kg	#2
Serial number of the instrument		

- #1 These markings are shown near the display of the result.
- #2 This marking is required if *T* is not equal to *Max*.

## 2. Description of Variant 1

#### approved on 8/04/13

Certain other capacities of the Ohaus model RS instruments as listed in Table 1 below (the pattern is shown in **bold**).

Model	Maximum Capacity ( <i>Max</i> )	Minimum Capacity ( <i>Min</i> )	Verification Scale Interval ( <i>e</i> )	Maximum Subtractive Tare Capacity ( <i>T</i> =)
RS-6S	6 kg	0.040 kg	0.002 kg	5.998 kg
RS-15S	15 kg	0.100 kg	0.005 kg	14.995 kg
RS-30S	30 kg	0.200 kg	0.01 kg	29.99 kg

TABLE	Ξ1
-------	----

## TEST PROCEDURE No 6/4D/368

Instruments shall be tested in accordance with any relevant tests specified in the National Instrument Test Procedures.

The instrument shall not be adjusted to anything other than as close as practical to zero error, even when these values are within the maximum permissible errors.

#### Maximum Permissible Errors

The maximum permissible errors are specified in Schedule 1 of the *National Trade Measurement Regulations 2009*.

### FIGURE 6/4D/368-1




Ohaus Model RS Weighing Instrument (with column-mounted customer display)

# FIGURE 6/4D/368-2




Model RS Weighing Instrument (with customer display directly mounted)

## FIGURE 6/4D/368-3



Ohaus Model RS Software Number and Version

## FIGURE 6/4D/368-4



**Typical Sealing Method** 

~ End of Document ~